

# Chemmaster

## Boilersuit with hood and elasticated wrists

Chemmaster provides excellent resistance to various acids, alkalis, and industrial chemicals due to its tough and durable 380gm<sup>2</sup> double coated PVC material. This makes it an ideal choice for a wide range of chemical handling operations.

### KEY FEATURES

- ▲ Ring-pull zip for easy donning and doffing when wearing gloves
- ▲ Double storm facing stud closure for increased protection
- ▲ Helmet-compatible hood
- ▲ Elasticated wrists ensure a snug and secure fit
- ▲ Garment can be reused if not contaminated or damaged
- ▲ Stitched and high frequency welded seams
- ▲ Tested to EN 14605 and ASTM F903

### COLOUR AVAILABLE



Green



### STANDARDS



EN 14605:2005  
+A1:2009



EN 14605:2005  
+A1:2009  
Type 3



EN 14605:2005  
+A1:2009  
Type 4

ASTM F903  
Resistance to Penetration by liquids.



### US TESTING DATA

Property	Test Method	Result
Basis Weight	ASTM D3776	380 g/m <sup>2</sup>
Resistance to penetration - Sodium Hydroxide (50%)	ASTM F903 Procedure A	Pass
Resistance to penetration - Hydrochloric Acid (37%)	ASTM F903 Procedure A	Pass
Resistance to penetration - Sodium Hypochlorite (15%)	ASTM F903 Procedure A	Pass

### SUITABLE INDUSTRIES & APPLICATIONS



- ▲ Chemical Cleaning
- ▲ Chemical Road Freight
- ▲ Chemical Site Handling
- ▲ Heavy Industry
- ▲ Oil and Gas
- ▲ Petrochem Refining
- ▲ Shipping
- ▲ Tank Cleaning

### PRODUCT OPTIONS

Item	Code	Colour	Hood	Collar	Elasticated Wrists	Elasticated Ankles
<b>Boilersuit</b>	CMBH	Green	✓	-	-	-
<b>Boilersuit</b>	CMBH-EW	Green	✓	-	✓	-
<b>Boilersuit</b>	CMBH-EWA	Green	✓	-	✓	✓
<b>Boilersuit</b> (Type 4 product)	CMBC-EW	Green	-	✓	✓	-



### SIZING - (Wearer's Measurements)

Size	Body Height (cm)	Chest (cm)	Waist (cm)	Inside Leg (cm)
<b>S</b>	166-170	90-98	81-89	73
<b>M</b>	170-174	98-106	89-97	75
<b>L</b>	174-179	106-114	97-104	78
<b>XL</b>	179-184	114-122	104-112	81
<b>2XL</b>	179-184	122-130	112-120	81
<b>3XL</b>	179-184	130-138	120-128	81
<b>4XL</b>	179-184	138-146	128-136	81

### STORAGE AND MAINTENANCE

We recommend storing Chemmaster garments in their original packaging, away from UV sources. After use, please follow the care instructions provided on the label. To remove any contamination, rinse the Chemmaster clothing with cold water and allow it to drip dry in a shaded area, away from UV sources. It is advisable to store Chemmaster clothing in a cool, dry, and clean environment.

**NOTE:** For hygiene purposes, it is recommended that the garment be worn by the same individual.

### CHEMICAL RESISTANCE DATA

For chemical permeation data, please contact our sales department at [sales@globusgroup.com](mailto:sales@globusgroup.com).

### COMPLIANCE STATEMENT - UK (UKCA)/EU (CE)

Product conforms to the requirement of: UK Regulation 2016/425 on PPE, brought into UK Law and amended & Regulation (EU) 2016/425 of the European Parliament and of the Council as Personal Protective Equipment (PPE).

Type-Examination, (Module B), Certificates issued by:

**UK** – SGS UK Ltd., Rossmore Business Park, Ellesmere Port, Cheshire, CH65 3EN, UK. [A.B. No. **0120**].

**EU** – SGS Fimko Oy, Takomotie 8, FI-00380, Helsinki, Finland. [N.B. No. **0598**].

PPE is subject to the conformity assessment procedure, conformity to type based on Quality Assurances of the production process, (Module D), under the surveillance of the Approved/Notified Body(ies):

**UK** – SGS UK Ltd., Rossmore Business Park, Ellesmere Port, Cheshire, CH65 3EN, UK. [A.B. No. **0120**].

**EU** – SGS Fimko Oy, Takomotie 8, FI-00380, Helsinki, Finland. [N.B. No. **0598**].

Economic Operator [EU]: Globus EMEA Ltd., 51 Dawson Street, Dublin, D02 AN25, Ireland.